US-Letter / 07.17



CERTIFICATE

No. U8V 021433 0593 Rev. 00

Holder of Certificate: Vicor Corporation

25 Frontage Road Andover MA 01810 USA

Certification Mark:



Information Technology Equipment **Product:**

DC to DC Converter

This product was voluntarily tested to the relevant safety requirements referenced on this certificate. It can be marked with the certification mark above. The mark must not be altered in any way. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC 17067. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL and a Standards Council of Canada accredited Certification body.

72130438-100 Test report no.:

Date, 2019-08-06

(William J. Stinson)

Mulling Hon



CERTIFICATE

No. U8V 021433 0593 Rev. 00

Model(s): BCM4414VD1E5135T02 / Type: HV VIA BCM;

BCM4414VG0F4440T02 / Type: UHV VIA BCM

Brand Name: VICOR

Tested CAN/CSA C22.2 No.60950-1:2007/A2:2014

UL 60950-1:2007/R:2014-10 according to: EN 60950-1:2006/A2:2013

Production 067768

Facility(ies):

Parameters: Rated Input Voltage: 400 VDC (260-410); 544 VDC (400-700)

Rated Output Voltage: 50 V DC (32.5-51.3); 34 V DC (25.0-43.75)

Rated Output Power: 1750 W; 1750 W Rated Output Current: 35 A; 40A Degree of Protection: IPX0

ш

N



CERTIFICATE

No. U8V 021433 0593 Rev. 00

High Voltage and Ultra High Voltage

VIA BCM Model Matrix: BCMaaaabccdwwxxyzz

Example: BCM4414VD1E5135T00

BCM	=	Consta	nt

Product Fu	nction	n	
ВСМ	Bus Converter Module		

aaaa = 4414

Package Size (Length x Width)		
4414	4.4 in x 1.4 in	
4914	4.9 in x 1.4 in	

b = V

Package Type	ackage Type	
٧	Chassis mount	
В	Board mount	

cc = D1

Max Input Voltage (range)		
D1	410 Vdc (260-410)	
G0	700 Vdc (400-700)	
H0	800 Vdc (500-800)	

d = E

Range Ra	tio (Vin high / Vin low), used to define low line
E	1.6
F	1.8

ww = 51

Maximun	Output Voltage (range)	****		
13	13 Vdc (8.1 - 12.8)	50	50 Vdc (31.2 - 50.0)	
26	26 Vdc (16.3 - 25.6)	51	51 Vdc (32.5 - 51.3)	
44	44 Vdc (25.0 - 43.75)			

xx = 35

Maximum	Output Current		
35	35A	62 / 63	62.5A
40	40A	A2 / A3	125A

.0000	Grade				
С	-20 to 100°C	T	-40 to 100°C	М	-55 to 100°C

zz = 00

Custome (any alpi	er Options, Communication type and pin type hanumeric, non-safety related, non-inclusive	for PCB mou	unt models les)
00	No options	09	Analog communication, long pins
01	Analog communication	10	Digital communication, long pins
02	Digital communication	13	Analog communication, extra-long pins
05	Analog communication, short pins	14	Digital communication, extra-long pins
06	Digital communication, short pins	AD	Digital communication, extra-long socket pins
		AE	Digital communication, extra-long socket pins

TÜV SÜD America Inc. • 10 Centennial Drive • Peabody • MA 01960 • USA

US-Letter / 07.17



CERTIFICATE

No. U8V 021433 0593 Rev. 00

Customer Special Part Number	Equivalent Standard Part Number
BCA400B500C1K8A31	BCM4914VD1E5135C02
BCA400B500T1K8A31	BCM4914VD1E5135T02
BCA400C500C1K8A31	BCM4914BD1E5135C06
BCA400C500T1K8A31	BCM4914BD1E5135T06
BCA400G500C1K8A31	BCM4914BD1E5135C10
BCA400G500T1K8A31	BCM4914BD1E5135T10

License Conditions:

The High Voltage and Ultra-High Voltage VIA BCM series of DC-DC converters are designed for building-in.

Conditions of Acceptability - When installed in the end use equipment, the following are among considerations to be made:

- 1. The housing of the VIA is required to be connected to protective earth in the end application.
- The output is separated from the input internally by reinforced insulation.
- The output is considered SELV for all models.
- The SELV output (-LO) of the high current models (62.5A and 125A) is internally connected to the housing to create an earthed SELV circuit in the end use product.
- The consequences of the circuit possibly being earthed at a second point should be considered in the end application per clause 2.9.4 NOTE 2.
- 6. A dielectric withstand test for Reinforced Insulation can't be performed on the final HV VIA assembly. See isolation drawings for construction details. A dielectric withstand test for Reinforced Insulation can be performed on the final UHV VIA assembly. See isolation drawings for construction details
- See de-rating curve for maximum output current vs. case temperature. Max case temperature assumes only single sided cooling with either the top or bottom side maintained at or below the maximum allowable temperature.
- The High Voltage VIA BCMs with Vin from 260-410V were evaluated with fast acting external fuse rated 10A, Littelfuse 487 series or Littelfuse 505. Fuse may be provided in optional wiring harness.
- The Ultra High Voltage VIA BCMs with Vin from 400-700V and 500-800V were evaluated with an external fuse rated 5A, Littelfuse SPF series rated 1000Vdc.
- 10. The UHV VIA BCM may be used with a Vicor AC-DC TPM (Three Phase VIA AIM) input module. This configuration was evaluated with a 600Vac / 5A Littelfuse KTK fuse placed on each of the 3 input phases. The KTK fuses are used in place of the SPF fuse specified in condition 9.
- 11. An external insulator or gap pad may be necessary to maintain the required Creepage and Clearance distances when the UHV VIA is attached to a conductive surface (chassis mounting or a heat sink).
- 12. Input capacitor discharge test to be evaluated as part of the end product